

## Product data sheet

### Characteristics

# INS62045

## Floor Outlet Box, OptiLine 70



### Main

|                             |  |
|-----------------------------|--|
| Range                       | OptiLine   |
| Product name                | OptiLine 70  |
| Device short name           | OL70   |
| Product type                | Floor outlet box   |
| Device application          | Installation   |
| Cabling installation system | Floor box  |
| Type of floor               | Raised floor<br>In-cavity floor<br>Carpet<br>Hollow core floor |
| Floor box shape             | Square   |
| Colour                      | Stainless steel  |

### Complementary

|                     |  |
|---------------------|--|
| Device presentation | Complete product                                   |
| Device mounting     | Floor mounted                                      |
| Product material    | Stainless steel stainless steel<br>Aluminium alloy |
| Height              | 80 mm  |
| Width               | 290 mm   |
| Depth               | 290 mm   |


### Environment

|                         |                                |
|-------------------------|--------------------------------|
| IP degree of protection | IP40                           |
| Maximum load            | 200 kg                         |
| Market segment          | Commercial<br>Office<br>School |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Height             | 30 cm  |
| Package 1 Width              | 40 cm  |
| Package 1 Length             | 40 cm  |
| Package 1 Weight             | 3000 g |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| EU RoHS Directive        | Not applicable, out of EU RoHS legal scope  |
| Environmental Disclosure |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile      | No need of specific recycling operations  |