

Product data sheet

Characteristics

ISM20501

Pole, OptiLine 70, tension-mounted, one-sided, natural, 4170-4570 mm



Main

Range	OptiLine
Product name	OptiLine 70
Cabling installation system	Pole
Product type	Pole
Type of pole	One-sided
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted

Complementary

Additional information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	4170...4570 mm
Depth	120 mm
Width	61 mm

Environment

Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating temperature	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	12.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	7.2 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	28
Package 2 Height	64.9 cm
Package 2 Width	120.0 cm
Package 2 Length	256.0 cm
Package 2 Weight	236.544 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------