

## Product data sheet

### Characteristics

# ISM20501

OptiLine 70 - pole - tension-mounted - one-sided - natural - 4170-4570 mm



### Main

|                             |                 |
|-----------------------------|-----------------|
| Range                       | OptiLine        |
| Product name                | OptiLine 70     |
| Cabling installation system | Pole            |
| Product type                | Pole            |
| Type of pole                | One-sided       |
| Pole/post surface finish    | Anodized        |
| Pole fixing mode            | Tension-mounted |

### Complementary

|                           |  |
|---------------------------|--|
| Additional information    | Adjustability of ceiling fixing 400 mm |
| Colour                    | Natural                                |
| Front opening size        | 70 mm                                  |
| Material                  | Aluminium anodized                     |
| Quantity package 1 / unit | Set of 1                               |
| Height                    | 4170...4570 mm                         |
| Depth                     | 120 mm                                 |
| Width                     | 61 mm                                  |

### Environment

|                         |  |
|-------------------------|--|
| Standards               | 73/23/EEC<br>93/68/EEC<br>IEC 1084-2-4<br>SS 424 10 32<br>EN-AW-6063 |
| Operating temperature   | -25...60 °C  |
| IP degree of protection | IP40   |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Weight             | 7.2 kg |
| Package 1 Height             | 10 cm  |
| Package 1 width              | 12 cm  |
| Package 1 Length             | 10 cm  |

### Offer Sustainability

|                          |  |
|--------------------------|--|
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile  |

## Contractual warranty

---

Warranty

18 months

---