

Product data sheet

Characteristics

ISM20506

OptiLine, OptiLine 70 - pole - tension-mounted
- two-sided - natural - 4170-4570 mm



Main

Range	OptiLine
Product name	OptiLine 70
Cabling installation system	Pole
Product type	Pole
Type of pole	Two-sided
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted

Complementary

Additional information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	4170...4570 mm
Depth	118 mm
Width	120 mm

Environment


Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating temperature	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.8 cm
Package 1 Width	12 cm
Package 1 Length	410 cm
Package 1 Weight	14 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	1
Package 2 Height	14 cm
Package 2 Width	17 cm
Package 2 Length	432 cm
Package 2 Weight	15 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	28

Package 3 Height	67 cm
Package 3 Width	120 cm
Package 3 Length	450 cm
Package 3 Weight	442 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------