


Product data sheet

Characteristics

ISM20819

OptiLine 45 OptiLine 70 - cable feeder - grey



Main

Cabling installation system	Pole Post
Product or component type	Cable feeder

Complementary

Type of pole	One installation box Two installation boxes Two-sided One-sided
Type of post	One-sided Two-sided
Colour tint	Grey (RAL 7030)
Quantity per set	Set of 10
Pole/post surface finish	Powder coated Anodized
Pole fixing mode	Tension-mounted
Fixing mode	Snap-fitted
Material	PVC (polyvinyl chloride)
Length	120 mm
Height	20 mm
Width	120 mm
Market segment	Small commercial Residential

Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	28 g
Package 1 Height	1.97 cm
Package 1 width	12 cm
Package 1 Length	12 cm
Unit Type of Package 2	BAG
Number of Units in Package 2	10

Package 2 Weight	374 g
Package 2 Height	8.8 cm
Package 2 width	12.5 cm
Package 2 Length	17.8 cm
Unit Type of Package 3	S03
Number of Units in Package 3	160
Package 3 Weight	6.47 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------