

Product data sheet

Characteristics

GV4AU027

MN - undervoltage release - 24 V AC 50/60Hz -
24 V DC - for TeSys GV4



Main

Range	TeSys
Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	TeSys GV4 TeSys BV4
Voltage release type	Undervoltage release
[Uc] control circuit voltage	24 V AC 50/60 Hz 24 V DC

Complementary

[Ui] rated insulation voltage	24 V conforming to IEC 60947-1
Threshold tripping voltage	< 0.35 Un failsafe opening 0.35...0.7 Un possible opening 0.85...1.1 Un enabled closing
Mounting mode	Internal mounting
Maximum inrush power in VA	7 VA
Maximum inrush power in W	2 W
Maximum hold-in power consumption in VA	7 VA
Maximum hold-in power consumption in W	2 W
Mechanical durability	20000 cycles
Operating time	< 50 ms
Connections - terminals	Spring terminals 1 0.5...1.5 mm ² - cable stiffness: flexible without cable end
Wire stripping length	8 mm

Environment

Quantity per set	Set of 1
------------------	----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	66 g
Package 1 Height	3.5 cm
Package 1 width	6 cm
Package 1 Length	8.5 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins