

Product data sheet

Characteristics

ISM20824

OptiLine 45, decorative stripe, orange



Main

Cabling installation system	Pole
Product or component type	Decorative stripe

Complementary

Type of pole	One-sided Two-sided
Type of post	One-sided Two-sided
Colour tint	Orange (RAL 2004)
Quantity per set	5 m
Pole/post surface finish	Powder coated Anodized
Pole fixing mode	Tension-mounted Free-standing
Material	Silicone rubber
Length	5000 mm
Diameter	3.5 mm
Market segment	Small commercial Residential

Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	16.000 cm
Package 1 Length	25.000 cm
Package 1 Weight	54.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm

Package 2 Length	40.000 cm
Package 2 Weight	1.567 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------