

Product data sheet

Characteristics

KBB40DF4420

Canalis - flexible length - 40 A - 2 m - 1 circuit - 3L + N + PE



Main

Range of product	Canalis
Product or component type	Busbar trunking
Busbar description	Flexible length
Product compatibility	KBB
Direction change type	3 dimensions
[Ie] rated operational current	40 A at 35 °C

Complementary

Device application	Power socket distribution Lighting
Thermal stress limit	900 kA ² .s
Maximum radiated magnetic field	2 pT
[Ue] rated operational voltage	230...400 V
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	690 V
[Icw] rated short-time withstand current	0.94 kA
[Ipk] rated peak withstand current	9.6 kA
THDI	0...15 % 40 A 15...33 % 32 A 33...100 % 28 A
Network frequency	50/60 Hz
Number of circuits	2
Mounting mode	By clips
Standards	IEC 61439-6 IEC 60439-2
Width	2.14 m
Depth	51 mm
Height	60 mm
Length	2 m
Product weight	1.9 kg

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK06 conforming to IEC 62262
Ambient air temperature for operation	0...35 °C without derating

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.6 kg
Package 1 Height	6 cm
Package 1 width	44 cm
Package 1 Length	61 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------