

Product data sheet

Characteristics

KBC10DCB20

Canalis, Tap off unit, Canalis KB, 10A, polarity L+N+PE/2L+PE, with phase selection, direct connection



Main

Range	Canalis
Product or component type	Tap-off unit
Device short name	KBC
Device application	Lighting
Range compatibility	Canalis (KBB) busbar trunking Canalis (KBA) busbar trunking
[Ie] rated operational current	10 A at 35 °C
[Ue] rated operational voltage	230...240 V
Network frequency	50/60 Hz
Tap-off unit polarity	L1 + N + PE L2 + N + PE L3 + N + PE L1 + L2 + PE L1 + L3 + PE L2 + L3 + PE
Tap-off unit connector type	With phase selection

Complementary

Colour	Cream (RAL 9001)
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	690 V
Protection type	Without protection
Width	1 m
Depth	62 mm
Height	60 mm
Net weight	65 g
Quantity per set	Set of 10
Standards	EN/IEC 61439-1 EN/IEC 61439-6

Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
-------------------------	---------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	6.000 cm
Package 1 Length	11.500 cm
Package 1 Weight	67.000 g
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Height	12.500 cm
Package 2 Width	13.600 cm
Package 2 Length	32.000 cm
Package 2 Weight	802.000 g
Unit Type of Package 3	P06
Number of Units in Package 3	500
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	40.075 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

