

Product data sheet

Characteristics

L5106D10UAR3

C-Bus-6 channel 10A architectural dimmer-with 3 RCD-universal



Main

Range	C-Bus
Product or component type	Dimmer
Device application	Control
Load type	Incandescent: 20 W (minimum)
Provided equipment	RCCB, 2
Number of channels	6

Complementary

Maximum leakage current	10 mA
[Us] rated supply voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting time	0.5 s
Rated breaking capacity	6 kA
[Ui] rated insulation voltage	500 V

Environment

Dielectric strength	2500 V
Directives	2004/108/EC - electromagnetic compatibility
Standards	AS/NZS CISPR 14-1 IEC 60439-1 IEC 60669-2-1 EN 61000-3-11 AS/NZS CISPR 15 EN 55014-1 EN 55015 EN 61000-3-5 EN 61000-3-2 AS/NZS 3439-1 EN 61000-3-3

Packing Units

Package 1 Weight	22.500 kg
Package 1 Height	61.800 cm
Package 1 width	32.200 cm
Package 1 Length	50.500 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.