

Product data sheet

Characteristics

L5106D10UAR6C

Clipsal C-Bus, Architectural Dimmer with 6 RCD Chassis, 6 Channel, 10A



Main

Range	C-Bus
Product or component type	Dimmer
Device application	Control
Load type	Incandescent: 20 W (minimum)
Number of channels	6

Complementary

[Us] rated supply voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting time	0.5 s
Rated breaking capacity	6 kA
[Ui] rated insulation voltage	500 V

Environment

Dielectric strength	2500 V
Directives	2004/108/EC - electromagnetic compatibility
Standards	EN 61000-3-3 EN 61000-3-2 EN 55015 IEC 60669-2-1 EN 55014-1 AS/NZS CISPR 14-1 AS/NZS 3439-1 EN 61000-3-11 EN 61000-3-5 AS/NZS CISPR 15 IEC 60439-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	61.8 cm
Package 1 Width	32.2 cm
Package 1 Length	50.5 cm
Package 1 Weight	18.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information