

Product data sheet

Characteristics

L5501RFCP

Clipsal C-Bus, Relay, DIN Rail Mounted, Fan Control, 240V AC, 1 Channel, 1.5A, Without C-Bus Power Supply



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Relay
Device application	Fan speed controller
Load type	Inductive

Complementary

Rated voltage	100...250 V AC 50/60 Hz
[Us] rated supply voltage	15...36 V DC
Nominal output power	350 W
Number of channels	1
Number of modules	3
Local signalling	LED
Connector type	Screw terminals
Device mounting	DIN rail
Width	210 mm
Height	75.5 mm
Depth	66 mm

Environment







IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	11.5 cm
Package 1 Length	15.5 cm
Package 1 Weight	273.0 g
Unit Type of Package 2	PAL
Number of Units in Package 2	240
Package 2 Height	103.0 cm
Package 2 Width	66.0 cm
Package 2 Length	67.5 cm
Package 2 Weight	91.6 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	8
Package 3 Height	20.6 cm
Package 3 Width	22.5 cm
Package 3 Length	33.0 cm
Package 3 Weight	2.72 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins