

Product data sheet

Characteristics

L5504D2U

Clipsal C-Bus, Dimmer, DIN Rail Mounted, Universal, 240V AC, 4 Channel, 2.5A, With C-Bus Power Supply



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Dimmer
Device application	Control
Device presentation	Basic element
Load type	Incandescent Halogen lamp Low voltage lamp with electronic transformer Low voltage lamp with iron-core transformer LED lamp
Load current	2.5 A per channel
Dimmer type	Leading edge Trailing edge

Complementary

Standby consumption	20 W
[Ue] rated operational voltage	220...240 V AC for dimmer 15...36 V DC for C-Bus
Power supply output current	200 mA
Network frequency	47...53 Hz
Communication network type	C-Bus
Maximum number of supported devices	10 per network
Input impedance	50 kOhm at 1 kHz
Isolation voltage	3.75 kV from C-Bus to mains
Starting time	5 s
Software function	Select network clock Select network burden Select time delay range
Number of modules	12
Local signalling	LED
Number of channels	4
Connector type	RJ45 for C-Bus RJ45 for remote override
Mounting support	DIN rail
Clamping connection capacity	1 x 2.5 mm ² 2 x 1.5 mm ²
Width	216 mm
Height	92 mm
Depth	63 mm
Net weight	593 g

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10 cm
Package 1 Width	10.5 cm
Package 1 Length	22.5 cm
Package 1 Weight	702 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins