

Product data sheet

Characteristics

L5508D1AP

8 CHANNEL DIMMER DIN LEARN



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Dimmer
Device application	Control
Device presentation	Basic element
Load type	Inductive

Complementary

[Ue] rated operational voltage	220...240 V AC
Network frequency	47...53 Hz
Nominal output power	230 W
Number of modules	12
Local signalling	LED
Number of channels	8
Mounting support	DIN rail
Size	Base: 215 x 85 x 65 mm





Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Package 1 Weight	0.752 kg
Package 1 Height	100.000 mm
Package 1 width	110.000 mm
Package 1 Length	219.000 mm

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins