

Product data sheet

Characteristics

L5508D1AP

Clipsal C-Bus, Dimmer, DIN Rail Mounted, Leading Edge, 240V AC, 8 Channel, 1A, Without C-Bus Power Supply



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Dimmer
Device application	Control
Device presentation	Basic element
Load type	Incandescent Low voltage lamp with electronic transformer
Load current	1 A per channel
Dimmer type	Leading edge

Complementary

Standby consumption	10 W
Network frequency	47...53 Hz 57...63 Hz
Communication network type	C-Bus
Maximum number of supported devices	100 per network
Input impedance	100 kOhm at 1 kHz
Isolation voltage	3.75 kV from C-Bus to mains
Starting time	5 s
Time delay range	0...33.5 min
Software function	Select network clock Select network burden Select time delay range
Number of modules	12
Local signalling	LED
Number of channels	8
Connector type	RJ45 for C-Bus RJ45 for remote override
Mounting support	DIN rail
Clamping connection capacity	1 x 2.5 mm ² 2 x 1.5 mm ²
Width	215 mm
Height	85 mm
Depth	65 mm
Net weight	675 g

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	10.8 cm
Package 1 Length	23.0 cm
Package 1 Weight	936.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins