

Product data sheet

Characteristics

L5508DSIP

C-Bus, DIN Rail Mounted, Dsi Gateway, 8 Channel, 12M Modules



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Dimmer
Device application	Control
Device presentation	Basic element
Provided equipment	300 mm patch cable
Load type	DSI ballast
Load current	200 mA per channel 270 mA total
Power supply output current	200 mA

Complementary

Communication interface	Digital serial interface
Value of setting	0...100 %
Network frequency	47...53 Hz 57...63 Hz
Communication network type	C-Bus
Maximum number of supported devices	100 per network
Input impedance	100 kOhm at 1 kHz
Isolation voltage	3.75 kV from C-Bus to mains
Number of outputs	100 per channel
Software function	Select network clock Select network burden Select time delay range
Control type	Local control push-button per channel
Number of modules	12
Local signalling	LED
Number of channels	8
Connector type	RJ45 for C-Bus RJ45 for remote override
Mounting support	DIN rail
Clamping connection capacity	1 x 2.5 mm ² 2 x 1.5 mm ²
Width	215 mm
Height	85 mm
Depth	65 mm







Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10 cm
Package 1 Width	10.5 cm
Package 1 Length	22.5 cm
Package 1 Weight	846 g
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	26 cm
Package 2 Width	22 cm
Package 2 Length	34 cm
Package 2 Weight	5.346 kg
Unit Type of Package 3	P12
Number of Units in Package 3	180
Package 3 Height	95 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	169.38 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins