

Product data sheet

Characteristics

GVAU115

Undervoltage release (MN), TeSys GV2-GV3,
110-115V AC 50Hz



Main

Range	TeSys
Device short name	GVAU
Product or component type	Undervoltage release

Complementary

Range compatibility	GV2ME GV2LE GV2L GV2P GV3L GV3P
[Uc] control circuit voltage	127 V AC 60 Hz 110...115 V AC 50 Hz
Control circuit voltage limits	0.85...1.1 Un
[Ui] rated insulation voltage	690 V AC conforming to IEC 60947-1 600 V AC conforming to UL 60947-4-1 600 V AC conforming to CSA C22.2 No 60947-4-1
Threshold tripping voltage	0.7...0.35 Un
Inrush power in VA	12 VA AC
Inrush power in W	8 W
Hold-in power consumption in VA	3.5 VA AC
Hold-in power consumption in W	1.1 W
Operating time	10...15 ms conforming to IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 cable(s) 1...2.5 mm ² solid Screw clamp terminals 2 cable(s) 1...2.5 mm ² solid Screw clamp terminals 1 cable(s) 0.75...2.5 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 0.75...2.5 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.75...1.5 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.75...1.5 mm ² flexible with cable end
Tightening torque	< 1.4 N.m on screw clamp terminals
Mechanical durability	10000 Cycles with GV3P and GV3L 30000 cycles with GV2ME and GV2P
Quantity per set	Set of 10
Height	89 mm
Width	18 mm
Depth	66 mm
Net weight	0.105 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

GVAU...

