

Product data sheet

Characteristics

IMT37412

Thorsman installation material, cavity fixing, TPP-10xM4K, set of 2, DIY



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TPP
Mounting support	Board material - thickness: 10...26 mm
Type of packing	Plastic bag and cardboard with eurohole
Quantity per set	Set of 2

Complementary

Thread type	M4
Screw length	50 mm
Drilling diameter	10 mm
Material	Toggle: zinc Collar: zinc Spring: steel Hook: steel electroplated
Practical load capacity	Pull-out load: 16 kg for 13 mm board 3) Pull-out load: 22 kg for 2 x 13 mm board 3)
Size	Hook: 9 x 16 x 29 mm
Length	95 mm
Width	20 mm
Net weight	0.014 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	1.5 cm
Package 1 Length	9.3 cm
Package 1 Weight	78 g
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	1.5 cm
Package 2 Width	20 cm
Package 2 Length	35 cm
Package 2 Weight	390 g
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Height	15 cm
Package 3 Width	30 cm

Package 3 Length	40 cm
Package 3 Weight	4.68 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations