

Product data sheet

Characteristics

LA1SK11

TeSys SK - auxiliary contact block - 1 NO + 1 NC



Main

Range	TeSys
Device short name	LA1SK
Product or component type	Auxiliary contact block
Product compatibility	LC1SK
Auxiliary contacts operation	Instantaneous
Pole contact composition	1 NO + 1 NC
Connections - terminals	Screw clamp terminals 1 cable(s) 1.5...6 mm ² solid Screw clamp terminals 2 cable(s) 1.5...4 mm ² solid Screw clamp terminals 1 cable(s) 0.5... 6 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.35... 2.5 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 0.35... 6 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 0.35... 1.5 mm ² flexible without cable end

Complementary

Mounting location	Front side
[Ui] rated insulation voltage	690 V conforming to IEC 60947 690 V conforming to BS 5424 690 V conforming to VDE 0110 group C 690 V conforming to CSA C22.2 No 14
[Ue] rated operational voltage	690 V AC <= 400 Hz
[Ith] conventional free air thermal current	10 A (at 55 °C)
Associated fuse rating	10 A gL conforming to IEC 60947 10 A gL conforming to VDE 0660
Tightening torque	0.8 N.m - on screw clamp terminals
Width	27 mm
Net weight	0.022 kg

Environment

Standards	VDE 0660 BS 5424 IEC 60947 NF C 63-110
Product certifications	CSA UL
IP degree of protection	IP2x
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-50...70 °C
Operating altitude	2000 m without derating

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------