

## Product data sheet

### Characteristics

# IMT37416

Thorsman installation material, cavity fixing,  
with screw, TSP-10/75, set of 5, DIY



### Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TSP
Provided equipment	Screw
Mounting support	Board material - thickness: 3...40 mm
Thread type	M5
Screw diameter	5 mm
Screw length	75 mm
Drilling diameter	10 mm
Colour tint	Blue/white

### Complementary

Quantity per set	Set of 5
Net weight	0.00196 kg

### Environment






Material	Screw: steel electroplated Collar: PA (polyamide) Spring: PA (polyamide)
Practical load capacity	Shear: 25 kg for 13 mm board 4.5) Pull-out load: 7.5 kg for 13 mm board 6) Shear: 40 kg for 2 x 13 mm board 4.5) Pull-out load: 15 kg for 2 x 13 mm board 6)
Thickness	0...37 Mm fixture 13 mm board 0...37 Mm fixture 2 x 13 mm board 0...24 mm
Environmental characteristic	Corrosion resistance
Type of packing	Plastic bag and cardboard with eurohole
Ambient air temperature for operation	-40...80 °C
Diameter	20 mm
Length	78 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	1.5 cm
Package 1 Length	9.3 cm
Package 1 Weight	17 g
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	2 cm
Package 2 Width	20 cm
Package 2 Length	35 cm

Package 2 Weight	324 g
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.092 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations