


Product data sheet

Characteristics

LA4DB2B

TeSys; TeSys D, suppressor module,
bidirectional peak limiting diode, 24 V AC



Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	4P LC1D40008...D80008 3P LC1D80...D95 4P LC1D80004

Complementary

Mounting location	Top
Mounting mode	By screws
Suppressor technology	Bidirectional peak limiting diode
[Uc] control circuit voltage	12...24 V AC 50/60 Hz
Maximum peak voltage	2 Uc
Net weight	0.018 kg




Environment


Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	4.2 cm
Package 1 Length	5 cm
Package 1 Weight	15 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months