

Product data sheet

Characteristics

IMT37420

Thorsman installation material, cavity fixing, with threaded screw, TMX-5E, set of 5, DIY



Main

| | |
|---------------------------|---|
| Range of product | Thorsman |
| Product or component type | Cavity fixing |
| Device short name | TMX |
| Provided equipment | Threaded screw |
| Mounting support | High load installation in board material - thickness: 6...13 mm |
| Thread type | M5 |
| Screw diameter | 5 mm |
| Screw length | 57 mm |
| Shape of screw head | Combi-head Cross slotted |
| Screwdriver shape | Philips |
| Drilling diameter | 10 mm |

Complementary

| | |
|------------------|-----------|
| Quantity per set | Set of 5 |
| Net weight | 0.0158 kg |

Environment

| | |
|---------------------------------------|--|
| Material | Screw: steel electroplated Cavity fixing: sheet metal electroplated |
| Practical load capacity | Shear: 40 kg 2.5) Pull-out load: 16 kg 3) |
| Thickness | 0...24 mm |
| Environmental characteristic | Fire resistance |
| Type of packing | Plastic bag and cardboard with eurohole |
| Ambient air temperature for operation | -40...80 °C |
| Diameter | 16 mm |
| Length | 62 mm |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.6 cm |
| Package 1 Width | 1.6 cm |
| Package 1 Length | 6.2 cm |
| Package 1 Weight | 16.0 g |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |