

Product data sheet

Characteristics

INS12904

OptiLine 50, cable shelf, PC/ABS, white



Main

Product or component type	Cable shelf
Quantity per set	24 m
Colour tint	White (RAL 9010)

Complementary

Trunking material	Plastic Aluminium
Fixing mode	Snap-fitted
Material	PC/ABS
Length	1000 mm
Height	17 mm
Width	48 mm

Environment



Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.7 cm
Package 1 Width	4.8 cm
Package 1 Length	100 cm
Package 1 Weight	88 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Contractual warranty	
Warranty	18 months