

Product data sheet

Characteristics

LA7D03N

TeSys D thermal overload relays - remote electrical tripping - 415...440V AC



Main

Range	TeSys
Product or component type	Electrical remote tripping
Device short name	LA7D
Accessory / separate part category	Electrical accessory
Product compatibility	LRD33.. LR3D35.. LR3D15.. LRD15.. LR3D33.. LR3D43.. LR2D LRD43..
[Uc] control circuit voltage	415/440 V AC 50/60 Hz

Complementary

Maximum inrush power in VA	100 VA
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	105 g
Package 1 Height	5 cm
Package 1 width	4.8 cm
Package 1 Length	4.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------