

Product data sheet

Characteristics

ISM11150

OptiLine 70, installation trunking, 80x55 mm, aluminium, natural, 2000 mm



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product or component type	Installation trunking
Colour tint	Natural
Quantity per set	6 m
Market segment	Residential Small commercial

Complementary

Trunking material	Aluminium
Trunking dimension	80 x 55 mm
Compartment partitioning	1 compartment
Fixing mode	By screws
Front opening size	70 mm
Material	Aluminium anodized
Length	2000 mm
Height	80 mm
Width	55 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15 cm
Package 1 Width	22.5 cm
Package 1 Length	200 cm
Package 1 Weight	5.16 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	15 cm
Package 2 Width	22.5 cm
Package 2 Length	206 cm
Package 2 Weight	924 kg

Unit Type of Package 3	P12
Number of Units in Package 3	90
Package 3 Height	56 cm
Package 3 Width	120 cm
Package 3 Length	205 cm
Package 3 Weight	16360 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------