

## Product data sheet

### Characteristics

# LAD4RC3E

## D40A to D65A RC 24-48V Suppressor



### Main

Range	TeSys TeSys Deca
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	3P LC1D40A...D80A 4P LC1DT60A...DT80A

### Complementary

Mounting location	Front
Mounting mode	By clips
Suppressor technology	RC circuit
[Uc] control circuit voltage	24...48 V AC 50/60 Hz
Maximum peak voltage	3 Uc
Product weight	0.02 kg
Colour	Dark grey

### Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	17 g
Package 1 Height	3 cm
Package 1 width	4 cm
Package 1 Length	6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	193 g
Package 2 Height	6.2 cm
Package 2 width	7.5 cm
Package 2 Length	12 cm
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Weight	2.134 kg
Package 3 Height	15 cm
Package 3 width	15 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------