

Product data sheet

Characteristics

KBA40ABG4

Feed unit for KBA, Canalis KBA, 40 A, left mounting



Main

Range of product	Canalis
Product or component type	Feed unit
Conductors material	Aluminium
[Ie] rated operational current	25 A 40 A
[Ue] rated operational voltage	230...400 V
Number of circuits	1
Protection type	Without protection
Control type	Without

Complementary

Provided equipment	End cover
Mounting location	Left
Mounting mode	By screws
Mounting support	Busbar
Connections - terminals	Terminal block - screw clamp connector for 10 mm ²
Width	300 mm
Depth	75.5 mm
Height	78.5 mm
Standards	IEC 60439-2 IEC 61439-6

Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------