

## Product data sheet

### Characteristics

# KBA40ABG4

Canalis, Feed unit for KBA - 40 A - left mounting



### Main

Range of product	Canalis
Product or component type	Feed unit
Conductors material	Aluminium
[Ie] rated operational current	25 A 40 A
[Ue] rated operational voltage	230...400 V
Number of circuits	1
Protection type	Without protection
Control type	Without

### Complementary

Provided equipment	End cover
Mounting location	Left
Mounting mode	By screws
Mounting support	Busbar
Connections - terminals	Terminal block - screw clamp connector for 10 mm <sup>2</sup>
Width	300 mm
Depth	75.5 mm
Height	78.5 mm
Standards	IEC 60439-2 IEC 61439-6

### Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	18 months
----------	-----------