

## Product data sheet

### Characteristics

# KBB25ED22305

Straight length, Canalis KBB, 25 A, 2 circuits L +N+PE, 5 tap-off units, 3 m

### Main

Range of product	Canalis
Product or component type	Busbar trunking
Product compatibility	KBB

### Complementary

Device application	Lighting Power socket distribution
Maximum radiated magnetic field	2 pT
[Ue] rated operational voltage	230...400 V
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	690 V
[Ie] rated operational current	25 A at 35 °C
Network frequency	50/60 Hz
[Icw] rated short-time withstand current	0.44 kA
[Ipk] rated peak withstand current	4.4 kA
Thermal stress limit	195 kA <sup>2</sup> .s
THDI	0...15 % 25 A 15...33 % 20 A 33...100 % 16 A
Maximum voltage drop	<0.72 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.67 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.61 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.55 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting mode	By screws
Busbar description	Straight length
Busbar trunking polarity	L + N + PE
Number of circuits	2
Number of tap-off outlets	5
Control type	Without
Standards	EN/IEC 60439-2 EN/IEC 61439-6
Width	3100 mm
Depth	51 mm
Height	60 mm
Length	3 m
Net weight	4.6 kg
Quantity per set	Set of 6

## Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
IK degree of protection	IK06 conforming to EN/IEC 62262
Ambient air temperature for operation	0...35 °C (100 % of In) 35...40 °C (96 % of In) 40...45 °C (93 % of In) 45...50 °C (89 % of In) 50...55 °C (85 % of In)

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.5 kg
Package 1 Height	6 cm
Package 1 width	5.1 cm
Package 1 Length	310 cm

## Contractual warranty

Warranty	18 months
----------	-----------