

Product data sheet

Characteristics

KBC10DCB20

Canalis - tap-off unit - 10A - phase selection - L +N+PE or L+L+PE



Main

Range	Canalis
Product or component type	Tap-off unit
Device short name	KBC
Product compatibility	KBB KBA
Device application	Lighting
Range compatibility	KBB busbar trunking KBA busbar trunking

Complementary

[Ue] rated operational voltage	230...240 V
[Ui] rated insulation voltage	690 V
[Ie] rated operational current	10 A at 35 °C
Network frequency	50/60 Hz
Protection type	Without protection
Busbar trunking polarity	L + N + PE L2 + L1 + L3 + PE L2 + N2 + L3 + PE
Tap-off unit polarity	L2+N L2+N2 L2+L3 L3+N3 L3+N L1+L2 L1+L3 L1+N
Tap-off unit connector type	With phase selection
Standards	EN/IEC 61439-6 EN/IEC 60439-2
Width	1 m
Depth	62 mm
Height	60 mm
Colour	Cream (RAL 9001)
Net weight	65 g
Quantity per set	Set of 10

Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
-------------------------	---------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

