

Product data sheet

Characteristics

KBC16DCF40

Canalis, - tap-off unit - 16A - 3L+N+PE - with protection



Main

Range	Canalis
Offer type	Classic Control system
Product or component type	Connector
Device application	Lighting
Range compatibility	Canalis KBA busbar trunking Canalis KBB busbar trunking
[Ie] rated operational current	16 A at 35 °C
[Ue] rated operational voltage	230...400 V
Network frequency	50/60 Hz
Busbar trunking polarity	L2 + L1 + L3 + N + PE
Protection type	Fuse
Fuse type	Cylindrical: 8.5 x 31.5 mm - gG conforming to NF
Communication port protocol	DALI
Tap-off unit polarity	3L+N+PE
Tap-off unit connector type	With fixed polarity
Provided equipment	Fuse not supplied
Colour	Cream (RAL 9001)

Complementary

[Ui] rated insulation voltage	690 V
Width	205 mm
Depth	38 mm
Height	68 mm
Net weight	90 g
Standards	EN/IEC 60439-2 EN/IEC 61439-6

Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
-------------------------	---------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	8.000 cm
Package 1 Length	17.000 cm
Package 1 Weight	229.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	18

Package 2 Height	15.800 cm
Package 2 Width	28.500 cm
Package 2 Length	43.500 cm
Package 2 Weight	4.613 kg
Unit Type of Package 3	P06
Number of Units in Package 3	144
Package 3 Height	73.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	38.976 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

