

Product data sheet

Characteristics

L5104D5

C-Bus Control and Management System, Dimmer Module, 4 Channel, Leading Edge, 250V, 5A



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Dimmer
Device application	Control
Device presentation	Basic element
Load type	Inductive

Complementary

Power consumption in VA	1200 VA
Network frequency	47...63 Hz
Nominal output power	1150 W
Local signalling	LED
Number of channels	4
Mounting support	Wall
Size	Base: 240 x 202 x 75 mm

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.606 cm
Package 1 Width	26.411 cm
Package 1 Length	24.825 cm
Package 1 Weight	2.441 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	25.6 cm
Package 2 Width	34.9 cm
Package 2 Length	40.2 cm
Package 2 Weight	10.36 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information