

Product data sheet

Characteristics

L5112D10UAR12C

Clipsal C-Bus, Architectural Dimmer with 12
RCD Chassis, 12 Channel, 10A



Main

Range	C-Bus
Product or component type	Dimmer
Device application	Control
Load type	Incandescent: 20 W (minimum)
Number of channels	12

Complementary

[Us] rated supply voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting time	0.5 s
Rated breaking capacity	6 kA
[Ui] rated insulation voltage	500 V




Environment

Dielectric strength	2500 V
Directives	2004/108/EC - electromagnetic compatibility
Standards	EN 55014-1 AS/NZS 3439-1 AS/NZS CISPR 15 IEC 60439-1 EN 61000-3-11 IEC 60669-2-1 EN 61000-3-2 AS/NZS CISPR 14-1 EN 61000-3-5 EN 61000-3-3 EN 55015

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	32.8 cm
Package 1 Width	61.7 cm
Package 1 Length	76.3 cm
Package 1 Weight	27.4 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	6
Package 2 Height	120.0 cm
Package 2 Width	80.0 cm
Package 2 Length	6.0 cm
Package 2 Weight	164.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information