

Product data sheet

Characteristics

L5501RFCP

C-BUS SWEEP FAN CONTROL RELAY



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Relay
Device application	Fan speed controller
Load type	Inductive

Complementary

Rated voltage	100...250 V AC 50/60 Hz
[Us] rated supply voltage	15...36 V DC
Nominal output power	350 W
Number of channels	1
Number of modules	3
Local signalling	LED
Connector type	Screw terminals
Device mounting	DIN rail
Width	210 mm
Height	75.5 mm
Depth	66 mm

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	273.0 g
Package 1 Height	8.0 cm
Package 1 width	11.5 cm
Package 1 Length	15.5 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	240
Package 2 Weight	91.6 kg
Package 2 Height	103.0 cm
Package 2 width	66.0 cm
Package 2 Length	67.5 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Weight	2.72 kg
Package 3 Height	20.6 cm

Package 3 width	22.5 cm
Package 3 Length	33.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins