


## Product data sheet

### Characteristics

# LA4DA2E

TeSys D - suppressor module - RC circuit -  
24...48 V AC



### Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	3P LC1D80...D150 4P LC1D80004...D115004 4P LC1D40008...D80008

### Complementary

Mounting location	Top
Mounting mode	By screws
Suppressor technology	RC circuit
[Uc] control circuit voltage	24...48 V AC 50/60 Hz
Maximum peak voltage	3 Uc
Net weight	0.018 kg

### Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	22 g
Package 1 Height	5 cm
Package 1 width	2.7 cm
Package 1 Length	4.1 cm
Unit Type of Package 2	S01
Number of Units in Package 2	78
Package 2 Weight	1.884 kg
Package 2 Height	15 cm
Package 2 width	15 cm
Package 2 Length	40 cm
Unit Type of Package 3	P06
Number of Units in Package 3	312
Package 3 Weight	15.68 kg
Package 3 Height	15 cm
Package 3 width	80 cm
Package 3 Length	60 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------