

Product data sheet

Characteristics

LA4KA1U

TeSys K - Suppressor module - RC circuit - 110...250 V



Main

Range	TeSys
Device short name	LA4K
Product or component type	Suppressor module
Product compatibility	CA2K LC1K LC7K

Complementary

Mounting location	Front side
Mounting mode	Clip-on
Suppressor technology	RC circuit
[Uc] control circuit voltage	110...250 V AC
Maximum peak voltage	3 Uc
Local signalling	LED
Quantity per set	Set of 5
Height	25 mm
Width	6 mm
Depth	22 mm
Net weight	0.01 kg

Environment

Standards	IEC 60947 VDE 0660 NF C 63-110 BS 5424
Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-50...80 °C

Packing Units

Package 1 Weight	0.005 kg
Package 1 Height	0.280 dm
Package 1 width	0.520 dm
Package 1 Length	0.430 dm

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------