

## Product data sheet

### Characteristics

# LA6DK20E

## auxiliary latch block TeSys D - 42...48 V DC/AC 50...60 Hz



### Main

Range	TeSys
Product or component type	Mechanical latch block
Product compatibility	LC1D80 LC1D95 LC1D115 LC1D150 LP1D80
[Uc] control circuit voltage	42/48 V AC 50/60 Hz 42/48 V DC





### Complementary

Mounting location	Front side
Tripping control	Electrical Manual
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1
Power required in VA	25 for AC circuit
Power required in W	30 W for DC circuit
Mechanical durability	500000 cycles
Maximum operating rate	1200 cyc/h
On-load factor	10 %
Net weight	0.09 kg

### Environment

Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 <a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

---

**Contractual warranty**

Warranty	18 months
----------	-----------

---