

## Product data sheet

### Characteristics

# LA7D03E

TeSys; TeSys Deca, thermal overload relays, remote electrical tripping, 48 V DC/AC



### Main

Range	TeSys
Product or component type	Electrical remote tripping
Device short name	LA7D
Accessory / separate part category	Electrical accessory
Product compatibility	LR3D35.. LRD43.. LRD33.. LR3D43.. LRD15.. LR2D LR3D15.. LR3D33..
[Uc] control circuit voltage	48 V AC 50/60 Hz 48 V DC

### Complementary

Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net weight	0.09 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	4.8 cm
Package 1 Length	4.8 cm
Package 1 Weight	105 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------