

## Product data sheet

### Characteristics

# LA7D03N

TeSys; TeSys Deca, thermal overload relays, remote electrical tripping, 415...440V AC



### Main

Range	TeSys
Product or component type	Electrical remote tripping
Device short name	LA7D
Accessory / separate part category	Electrical accessory
Product compatibility	LRD33.. LR3D35.. LR3D15.. LRD15.. LR3D33.. LR3D43.. LR2D LRD43..
[Uc] control circuit voltage	415/440 V AC 50/60 Hz

### Complementary

Maximum inrush power in VA	100 VA
Net weight	0.09 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	4.8 cm
Package 1 Length	4.8 cm
Package 1 Weight	105 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------