


Product data sheet

Characteristics

LAD4RCE

RC CIR-CLIP ON CONTACTOR D09.38 3P 24/



Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	3P LC1D09...D38 4P LC1DT20...DT40 4P LC1D098...D258 CAD32, CAD50

Complementary

Mounting location	Side
Mounting mode	By clips
Suppressor technology	RC circuit
[Uc] control circuit voltage	24...48 V AC 50/60 Hz
Maximum peak voltage	3 Uc
Product weight	0.012 kg

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	14 g
Package 1 Height	1.5 cm
Package 1 width	8 cm
Package 1 Length	4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	140 g
Package 2 Height	6 cm
Package 2 width	10 cm
Package 2 Length	10 cm
Unit Type of Package 3	P06
Number of Units in Package 3	2240
Package 3 Weight	39.86 kg
Package 3 Height	77 cm
Package 3 width	60 cm
Package 3 Length	80 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------