

Product data sheet

Characteristics

LAD4V3U

TeSys D - suppressor module - varistor - 110...250 V AC/DC



Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	3P LC1D40A...D80A 4P LC1DT60A...DT80A

Complementary

Mounting location	Front
Mounting mode	By clips
Suppressor technology	Varistor (peak limiting)
[Uc] control circuit voltage	110...250 V DC 110...250 V AC 50/60 Hz
Maximum peak voltage	2 Uc
Net weight	0.02 kg

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	19 g
Package 1 Height	2 cm
Package 1 width	2 cm
Package 1 Length	6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	195 g
Package 2 Height	6.2 cm
Package 2 width	7.5 cm
Package 2 Length	12 cm
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Weight	2.183 kg
Package 3 Height	15 cm
Package 3 width	15 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------