

Product data sheet

Characteristics

LAD6K10M

CONTACTOR MECH. LATCH CONTACT BLOCK IEC



Main

Range	TeSys
Product or component type	Mechanical latch block
Product compatibility	TeSys D control relays LC1D40A...D65A LC1D09...D38 LC1DT60A...DT80A LC1DT20...DT40
[Uc] control circuit voltage	220/240 V AC 50/60 Hz 220/240 V DC

Complementary

Mounting location	Front side
Tripping control	Electrical Manual
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1
Power required in VA	25 for AC circuit
Power required in W	30 W for DC circuit
Mechanical durability	500000 cycles
Maximum operating rate	1200 cyc/h
On-load factor	10 %
Net weight	0.07 kg

Environment

Product certifications	UL CSA
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	97 g
Package 1 Height	4.7 cm
Package 1 width	5.2 cm
Package 1 Length	6.5 cm
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Weight	3.328 kg
Package 2 Height	15 cm
Package 2 width	15 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------