

## Product data sheet

### Characteristics

# LAD703B

Thermal Overload Relays, TeSys LR9, remote electrical stop, 24 V DC/AC

#### Main

Range	TeSys
Product or component type	Electrical remote stop
Device short name	LAD
Accessory / separate part category	Electrical accessory
Product compatibility	LRD313...LRD365 LR3D313...LR3D365 LR3D01...D35 LRD01...35 LR9G
[Uc] control circuit voltage	24 V AC 50/60 Hz 24 V DC

#### Complementary

Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net weight	0.09 kg

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	4.9 cm
Package 1 Length	5.3 cm
Package 1 Weight	110.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.705 kg

#### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

#### Contractual warranty

Warranty	18 months
----------	-----------