

Product data sheet

Characteristics

LAD703B

TeSys Deca thermal overload relays - remote electrical stop - 24 V DC/AC



Main

Range	TeSys
Product or component type	Electrical remote stop
Device short name	LAD
Accessory / separate part category	Electrical accessory
Product compatibility	LRD313...LRD365 LR3D313...LR3D365 LR3D01...D35 LRD01...35 LR9G
[Uc] control circuit voltage	24 V AC 50/60 Hz 24 V DC



Complementary

Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	110.0 g
Package 1 Height	4.9 cm
Package 1 width	4.9 cm
Package 1 Length	5.3 cm
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Weight	3.705 kg
Package 2 Height	15 cm
Package 2 width	15 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty

18 months
