

## Product data sheet

### Characteristics

# LC1DT20BD

TeSys D contactor - 4P(4 NO) - AC-1 -  $\leq 440$   
V 20 A - 24 V DC standard coil





## Main

|   |  |
|---|--|
| Range                                       | TeSys  |
| Product name                                | TeSys D  |
| Product or component type                   | Contacteur   |
| Device short name                           | LC1D   |
| Contacteur application                      | Resistive load   |
| Utilisation category                        | AC-1   |
| Poles description                           | 4P   |
| Power pole contact composition              | 4 NO   |
| [Ue] rated operational voltage              | Power circuit: ≤ 690 V AC 25...400 Hz<br>Power circuit: ≤ 300 V DC   |
| [Ie] rated operational current              | 20 A (at <60 °C) at ≤ 440 V AC AC-1 for power circuit  |
| Control circuit type                        | DC standard  |
| [Uc] control circuit voltage                | 24 V DC  |
| Auxiliary contact composition               | 1 NO + 1 NC  |
| [Uimp] rated impulse withstand voltage      | 6 kV conforming to IEC 60947   |
| Overvoltage category                        | III  |
| [Ith] conventional free air thermal current | 10 A (at 60 °C) for signalling circuit<br>20 A (at 60 °C) for power circuit  |
| Irms rated making capacity                  | 140 A AC for signalling circuit conforming to IEC 60947-5-1<br>250 A DC for signalling circuit conforming to IEC 60947-5-1<br>250 A at 440 V for power circuit conforming to IEC 60947   |
| Rated breaking capacity                     | 250 A at 440 V for power circuit conforming to IEC 60947   |
| [Icw] rated short-time withstand current    | 30 A 40 °C - 10 min for power circuit<br>61 A 40 °C - 1 min for power circuit<br>105 A 40 °C - 10 s for power circuit<br>210 A 40 °C - 1 s for power circuit<br>100 A - 1 s for signalling circuit<br>120 A - 500 ms for signalling circuit<br>140 A - 100 ms for signalling circuit |
| Associated fuse rating                      | 10 A gG for signalling circuit conforming to IEC 60947-5-1<br>25 A gG at ≤ 690 V coordination type 1 for power circuit<br>20 A gG at ≤ 690 V coordination type 2 for power circuit   |
| Average impedance                           | 2.5 mOhm - Ith 20 A 50 Hz for power circuit  |
| [Ui] rated insulation voltage               | Power circuit: 600 V CSA certified<br>Power circuit: 600 V UL certified<br>Signalling circuit: 690 V conforming to IEC 60947-1<br>Signalling circuit: 600 V CSA certified<br>Signalling circuit: 600 V UL certified<br>Power circuit: 690 V conforming to IEC 60947-4-1              |
| Power dissipation per pole                  | 1.56 W AC-1  |
| Front cover                                 | With   |
| Mounting support                            | Plate<br>Rail  |
| Standards                                   | CSA C22.2 No 14<br>EN 60947-4-1<br>EN 60947-5-1<br>IEC 60947-4-1<br>IEC 60947-5-1<br>UL 508  |

|                          |  |
|--------------------------|--|
| Product certifications   | GOST<br>LROS (Lloyds register of shipping)<br>UL<br>CSA<br>RINA<br>BV<br>CCC<br>DNV<br>GL  |
| Connections - terminals  | Control circuit: screw clamp terminals 2 cable(s) 1...<br>2.5 mm <sup>2</sup> flexible with cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> flexible without cable end<br>Control circuit: screw clamp terminals 2 cable(s) 1...<br>4 mm <sup>2</sup> flexible without cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> flexible with cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> solid without cable end<br>Control circuit: screw clamp terminals 2 cable(s) 1...<br>4 mm <sup>2</sup> solid without cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> flexible without cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...<br>4 mm <sup>2</sup> flexible without cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> flexible with cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...<br>2.5 mm <sup>2</sup> flexible with cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> solid without cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...<br>4 mm <sup>2</sup> solid without cable end |
| Tightening torque        | Control circuit: 1.7 N.m - on screw clamp terminals -<br>with screwdriver flat Ø 6 mm<br>Control circuit: 1.7 N.m - on screw clamp terminals -<br>with screwdriver Philips No 2<br>Power circuit: 1.7 N.m - on screw clamp terminals -<br>with screwdriver flat Ø 6 mm<br>Power circuit: 1.7 N.m - on screw clamp terminals -<br>with screwdriver Philips No 2   |
| Operating time           | 16...24 ms opening<br>53.55...72.45 ms closing   |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load<br>conforming to EN/ISO 13849-1<br>B10d = 20000000 cycles contactor with mechanical<br>load conforming to EN/ISO 13849-1   |
| Mechanical durability    | 30 Mcycles   |
| Maximum operating rate   | 3600 cyc/h 60 °C   |

## Complementary

|                                |  |
|--------------------------------|--|
| Coil technology                | Built-in bidirectional peak limiting diode suppressor  |
| Control circuit voltage limits | 0.1...0.25 U <sub>c</sub> (-40...70 °C):drop-out DC<br>0.7...1.25 U <sub>c</sub> (-40...60 °C):operational DC<br>1...1.25 U <sub>c</sub> (60...70 °C):operational DC |
| Time constant                  | 28 ms  |
| Inrush power in W              | 5.4 W (at 20 °C)   |
| Hold-in power consumption in W | 5.4 W at 20 °C   |
| Auxiliary contacts type        | Type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1<br>Type mirror contact 1 NC conforming to IEC 60947-4-1   |
| Signalling circuit frequency   | 25...400 Hz  |
| Minimum switching current      | 5 mA for signalling circuit  |
| Minimum switching voltage      | 17 V for signalling circuit  |
| Non-overlap time               | 1.5 Ms on de-energisation between NC and NO contact<br>1.5 ms on energisation between NC and NO contact  |
| Insulation resistance          | > 10 MOhm for signalling circuit   |
| Contact compatibility          | M7   |
| Compatibility code             | LC1D   |

## Environment

|                                       |  |
|---------------------------------------|--|
| IP degree of protection               | IP20 front face conforming to IEC 60529  |
| Protective treatment                  | TH conforming to IEC 60068-2-30  |
| Pollution degree                      | 3  |
| Ambient air temperature for operation | -40...60 °C<br>60...70 °C with derating  |
| Ambient air temperature for storage   | -60...80 °C  |
| Operating altitude                    | 0...3000 m   |
| Fire resistance                       | 850 °C conforming to IEC 60695-2-1   |
| Flame retardance                      | V1 conforming to UL 94   |
| Mechanical robustness                 | Vibrations contactor open: 2 Gn, 5...300 Hz<br>Vibrations contactor closed: 4 Gn, 5...300 Hz<br>Shocks contactor closed: 15 Gn for 11 ms<br>Shocks contactor open: 10 Gn for 11 ms |
| Height                                | 85 mm  |
| Width                                 | 45 mm  |
| Depth                                 | 99 mm  |
| Net weight                            | 0.365 kg   |

## Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Weight             | 556 g  |
| Package 1 Height             | 5.5 cm |
| Package 1 width              | 9.5 cm |
| Package 1 Length             | 12 cm  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End Of Life Information</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| PVC free                   | Yes   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|