

## Product data sheet

### Characteristics

# LC1D65008F7

TeSys Deca contactor , 4P(2 NO + 2 NC) ,  
AC-1 <= 440V, 80 A 110V AC 50/60 Hz coil





## Main

|   |  |
|---|--|
| Range                                       | TeSys  |
| Product name                                | TeSys D<br>TeSys Deca  |
| Product or component type                   | Contacteur   |
| Device short name                           | LC1D   |
| Contacteur application                      | Resistive load   |
| Utilisation category                        | AC-1   |
| Poles description                           | 4P   |
| Power pole contact composition              | 2 NO + 2 NC  |
| [Ue] rated operational voltage              | Power circuit: <= 690 V AC 25...400 Hz<br>Power circuit: <= 300 V DC   |
| [Ie] rated operational current              | 80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit   |
| Control circuit type                        | AC at 50/60 Hz   |
| [Uc] control circuit voltage                | 110 V AC 50/60 Hz  |
| [Uimp] rated impulse withstand voltage      | 6 kV conforming to IEC 60947   |
| Overtoltage category                        | III  |
| [Ith] conventional free air thermal current | 80 A (at 60 °C) for power circuit  |
| Irms rated making capacity                  | 1000 A at 440 V for power circuit conforming to IEC 60947  |
| Rated breaking capacity                     | 1000 A at 440 V for power circuit conforming to IEC 60947  |
| [Icw] rated short-time withstand current    | 520 A 40 °C - 10 s for power circuit<br>900 A 40 °C - 1 s for power circuit<br>110 A 40 °C - 10 min for power circuit<br>260 A 40 °C - 1 min for power circuit |
| Associated fuse rating                      | 125 A gG at <= 690 V coordination type 1 for power circuit<br>125 A gG at <= 690 V coordination type 2 for power circuit                                       |
| Average impedance                           | 1.5 mOhm - Ith 80 A 50 Hz for power circuit  |
| [Ui] rated insulation voltage               | Power circuit: 600 V CSA certified<br>Power circuit: 600 V UL certified<br>Power circuit: 690 V conforming to IEC 60947-4-1                                    |
| Electrical durability                       | 1.4 Mcycles 80 A AC-1 at Ue <= 440 V   |
| Power dissipation per pole                  | 9.6 W AC-1   |
| Front cover                                 | Without  |
| Mounting support                            | Rail<br>Plate  |
| Standards                                   | CSA C22.2 No 14<br>EN 60947-4-1<br>EN 60947-5-1<br>IEC 60947-4-1<br>IEC 60947-5-1<br>UL 508  |
| Product certifications                      | UL<br>CCC<br>GL<br>LROS (Lloyds register of shipping)<br>GOST<br>CSA<br>RINA<br>BV<br>DNV  |

|                          |  |
|--------------------------|--|
| Connections - terminals  | Control circuit: screw clamp terminals 2 cable(s) 1...<br>2.5 mm <sup>2</sup> flexible with cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> flexible without cable end<br>Control circuit: screw clamp terminals 2 cable(s) 1...<br>4 mm <sup>2</sup> flexible without cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> flexible with cable end<br>Control circuit: screw clamp terminals 1 cable(s) 1...<br>4 mm <sup>2</sup> solid without cable end<br>Control circuit: screw clamp terminals 2 cable(s) 1...<br>4 mm <sup>2</sup> solid without cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...<br>35 mm <sup>2</sup> flexible without cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...<br>25 mm <sup>2</sup> flexible without cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...<br>35 mm <sup>2</sup> flexible with cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...<br>25 mm <sup>2</sup> flexible with cable end<br>Power circuit: screw clamp terminals 1 cable(s) 1...<br>35 mm <sup>2</sup> solid without cable end<br>Power circuit: screw clamp terminals 2 cable(s) 1...<br>25 mm <sup>2</sup> solid without cable end |
| Tightening torque        | Control circuit: 1.7 N.m - on screw clamp terminals -<br>with screwdriver flat Ø 6 mm<br>Control circuit: 1.7 N.m - on screw clamp terminals -<br>with screwdriver Philips No 2<br>Power circuit: 8 N.m - on screw clamp terminals -<br>cable 25...35 mm <sup>2</sup> hexagonal screw head 4 mm<br>Power circuit: 5 N.m - on screw clamp terminals -<br>cable 1...25 mm <sup>2</sup> hexagonal screw head 4 mm<br>Control circuit: 1.7 N.m - on screw clamp terminals -<br>with screwdriver pozidriv No 2  |
| Operating time           | 4...19 ms opening<br>12...26 ms closing  |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load<br>conforming to EN/ISO 13849-1<br>B10d = 2000000 cycles contactor with mechanical<br>load conforming to EN/ISO 13849-1  |
| Mechanical durability    | 6 Mcycles  |
| Maximum operating rate   | 3600 cyc/h 60 °C   |

## Complementary

|                                 |   |
|---------------------------------|---|
| Coil technology                 | Without built-in suppressor module  |
| Control circuit voltage limits  | 0.3...0.6 Uc (-40...70 °C):drop-out AC 50/60 Hz<br>0.8...1.1 Uc (-40...60 °C):operational AC 50 Hz<br>0.85...1.1 Uc (-40...60 °C):operational AC 60 Hz<br>1...1.1 Uc (60...70 °C):operational AC 50/60 Hz |
| Inrush power in VA              | 140 VA 60 Hz cos phi 0.75 (at 20 °C)<br>160 VA 50 Hz cos phi 0.75 (at 20 °C)  |
| Hold-in power consumption in VA | 13 VA 60 Hz cos phi 0.3 (at 20 °C)<br>15 VA 50 Hz cos phi 0.3 (at 20 °C)  |
| Heat dissipation                | 4...5 W at 50/60 Hz   |

## Environment

|                                       |  |
|---------------------------------------|--|
| IP degree of protection               | IP20 front face conforming to IEC 60529  |
| Climatic withstand                    | Conforming to IACS E10   |
| Protective treatment                  | TH conforming to IEC 60068-2-30  |
| Pollution degree                      | 3  |
| Ambient air temperature for operation | -40...60 °C<br>60...70 °C with derating  |
| Ambient air temperature for storage   | -60...80 °C  |
| Operating altitude                    | 0...3000 m   |
| Fire resistance                       | 850 °C conforming to IEC 60695-2-1   |
| Mechanical robustness                 | Vibrations contactor open: 2 Gn, 5...300 Hz<br>Vibrations contactor closed: 4 Gn, 5...300 Hz<br>Shocks contactor closed: 15 Gn for 11 ms<br>Shocks contactor open: 10 Gn for 11 ms |

|            |         |
|------------|---------|
| Height     | 127 mm  |
| Width      | 85 mm   |
| Depth      | 125 mm  |
| Net weight | 1.45 kg |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Weight             | 1.456 kg |
| Package 1 Height             | 11.2 cm  |
| Package 1 width              | 13.5 cm  |
| Package 1 Length             | 15.2 cm  |
| Unit Type of Package 2       | S02      |
| Number of Units in Package 2 | 5        |
| Package 2 Weight             | 7.594 kg |
| Package 2 Height             | 15.0 cm  |
| Package 2 width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 3 Height             | 73.5 cm  |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End Of Life Information</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| PVC free                   | Yes   |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|