

## Product data sheet

### Characteristics

# LE1M35U706

TeSys LE - enclosed DOL starter - 0.8...1.2 A - 240 V AC coil



### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1M
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Contacteur Earth terminal Neutral terminal Thermal overload relay
Thermal protection adjustment range	0.8...1.2 A
Motor power kW	0.18 kW at 240 V AC 50/60 Hz 0.37 kW at 415 V AC 50/60 Hz 0.18 kW at 220/230 V AC 50/60 Hz 0.37 kW at 380/400 V AC 50/60 Hz
[Uc] control circuit voltage	240 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O

### Complementary

Local signalling	Operating: LED (yellow)
Cable entry number	2 ISO20 top 2 ISO25 top 2 Pg 13 top 2 Pg 21 top 2 ISO20 bottom 2 ISO25 bottom 2 Pg 13 bottom 2 Pg 21 bottom 2 Pg 16 top 2 Pg 16 bottom
Width	78 mm
Height	160 mm
Depth	108 mm
Net weight	0.6 kg

### Environment

Material	ABS (acrylonitrile butadiene-styrene)
IP degree of protection	IP65 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	600 g
Package 1 Height	16.8 cm
Package 1 width	8 cm
Package 1 Length	11.5 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------