

Product data sheet

Characteristics

LR9D5367

TeSys LRD thermal overload relays - 60...100 A - class 10



Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Electronic thermal overload relay
Device short name	LR9D
Relay application	Motor protection
Product compatibility	LC1D115 LC1D150 NSX circuit breaker
Network type	AC
Signalling function	Alarm
Thermal protection adjustment range	60...100 A
[Ui] rated insulation voltage	Power circuit: 1000 V conforming to IEC 60947-4-1 Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL

Complementary

Network frequency	50...60 Hz
[Us] rated supply voltage	24 V DC
Supply voltage limits	17...32 V
Mounting support	Under contactor Rail
Tripping threshold	1.05 +/- 0.06 In alarm conforming to IEC 60947-4-1 1.12 +/- 0.06 In de-energisation conforming to IEC 60947-4-1
[Ith] conventional free air thermal current	5 A for signalling circuit
[Ue] rated operational voltage	690 V 50...60 Hz
Associated fuse rating	5 A gG for signalling circuit
[Uimp] rated impulse withstand voltage	6 kV IEC 61000-4-5
Phase failure sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1
Control type	Red push-button: stop Blue push-button: reset
Temperature compensation	-20...60 °C
Switching capacity in mA	0...150 mA
Maximum voltage drop	<2.5 V closed state
Connections - terminals	Power circuit: bars Control circuit: screw clamp terminals 1 cable(s) 0.5...1.5 mm ² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 0.5...1.5 mm ² flexible without cable end Alarm circuit: screw clamp terminals 1 cable(s) 0.5...1.5 mm ² flexible without cable end
Tightening torque	Alarm circuit: 0.45 N.m - on screw clamp terminals Power circuit: 18 N.m - on bars M8 Control circuit: 1.2 N.m - on screw clamp terminals
Depth	132 mm
Net weight	0.885 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...60 °C without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-60...70 °C
Operating altitude	<= 2000 m without derating
Mechanical robustness	Vibrations: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6 Shocks: 13 Gn for 11 ms conforming to IEC 60068-2-7
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Standards	VDE 0660 IEC 60947-4-1 IEC 255-8 EN 60947-4-1 IEC 255-17
Product certifications	CSA 22-2 UL 508

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	922 g
Package 1 Height	13 cm
Package 1 width	15 cm
Package 1 Length	16 cm
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Weight	11.91 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------