

## Product data sheet

### Characteristics

# LX1D6U5

TeSys; TeSys Deca, contactor coil, LX1D6,  
240 V AC 50 Hz for 80 & 95 A contactor



### Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D6
Control circuit type	AC at 50 Hz
[Uc] control circuit voltage	240 V AC 50 Hz
Average resistance	152 Ohm at 20 °C
Inductance of closed circuit	8.7 H
Product compatibility	LC1D95 LC1D80
Mechanical durability	10 Mcycles
Maximum operating rate	3600 cyc/h 60 °C

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.3...0.6 Uc at 50/60 Hz (at <55 °C) Operational: 0.8...1.1 Uc at 50 Hz (at <55 °C) Operational: 0.85...1.1 Uc at 60 Hz (at <55 °C)
Inrush power in VA	200 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-in power consumption in VA	20 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	6...10 W at 50/60 Hz

### Environment

Ambient air temperature for operation	-5...60 °C
Net weight	0.28 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	12.6 cm
Package 1 Length	5.4 cm
Package 1 Weight	307.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	16
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.567 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------