

## Product data sheet

### Characteristics

## LXD1X7

TeSys; TeSys Deca, contactor coil, LXD1, 600 V AC 50/60 Hz for 9... 38 A contactor



### Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LXD1
Control circuit type	AC at 50/60 Hz
[Uc] control circuit voltage	600 V AC 50/60 Hz
Average resistance	3810 Ohm at 20 °C
Inductance of closed circuit	136 H
Product compatibility	LC1D09...D38 CAD LC1DT20...DT40
Mechanical durability	15 Mcycles
Maximum operating rate	3600 cyc/h 60 °C

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.3...0.6 Uc at 50/60 Hz (at <60 °C) Operational: 0.8...1.1 Uc at 50 Hz (at <60 °C) Operational: 0.85...1.1 Uc at 60 Hz (at <60 °C)
Inrush power in VA	70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-in power consumption in VA	7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	2...3 W at 50/60 Hz







### Environment

Ambient air temperature for operation	-5...60 °C
Net weight	0.07 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	4.5 cm
Package 1 Length	3.5 cm
Package 1 Weight	79.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------